



MasterColor CDM PAR38

MasterColor CDM100/PAR38/FL/4K ALTO ELITE 12PK

Philips MasterColor® Ceramic Metal Halide PAR38 Lamps offer high-efficiency, ceramic metal halide reflector lamps with a stable color over lifetime and a crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Color rendering index (CRI)	
Cap-Base	E26 [Single Contact Medium Screw]	92	
Operating Position	UNIVERSAL [Any or Universal (U)]		
Life to 50% Failures (Nom)	16,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	940 [CCT of 4000K]	Power Consumption	95.0 W
Beam Angle (Nom)	25 degree(s)	Voltage (Nom)	102 V
Luminous Intensity (Nom)	20,000 cd	Voltage (Nom)	102 V
Color Designation	Cool White (CW)		
Chromaticity Coordinate X (Nom)	0.380	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	0.375	Dimmable	No
Correlated Color Temperature (Nom)	4200 K	Mechanical and Housing	
		Bulb Finish	Clear

MasterColor CDM PAR38

Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Product Data	
Order product name	CDM100/PAR38/FL/4K ALTO ELITE 12PK
Full product name	MasterColor CDM100/PAR38/FL/4K ALTO ELITE 12PK
Order code	456533


Material Nr. (12NC)	928494230901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677456535
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677456530

Dimensional drawing




Product	D	D	C (max)
CDM100/PAR38/FL/4K ALTO ELITE 12PK	4.76 inch	121.0 mm	134.0 mm

Lifetime



Life Expectancy Diagram - CDM100/PAR38/FL/4K ALTO ELITE 12PK



Lumen Maintenance Diagram - CDM100/PAR38/FL/4K ALTO ELITE 12PK

