



Ceramalux ALTO

SON 400W E39 ED58 CL SLV/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	20
Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V
Voltage (Nom)	100 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	SON 400W E39 ED58 CL SLV/12
Full product name	SON 400W E39 ED58 CL SLV/12
Order code	928601139301
Material Nr. (12NC)	928601139301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368814
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677368819

Ceramalux ALTO

Dimensional drawing

Product

SON 400W E39 ED58 CL SLV/12

