



# Ceramalux ALTO

## C150S56/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	526
Chromaticity Coordinate Y (Nom)	419
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	96 lm/W
Luminous Efficacy (rated) (Nom)	103 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Lamp Current (Nom)	1.8 A
Voltage (Nom)	100 V
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED28
Approval and Application	
Mercury (Hg) Content (Max)	22.1 mg
Product Data	
Order product name	C150S56/ALTO 12PK
Full product name	C150S56/ALTO 12PK
Order code	368761
Material Nr. (12NC)	928601139601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368760
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677368765

Ceramalux ALTO

Dimensional drawing

Product
C150S56/ALTO 12PK

