



# Ceramalux ALTO

## SON 150W E39 ED75 CL SLV/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | E39 [Single Contact Mogul Screw] |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Features                           | ALTO® (ALTO)                     |
| Light Technical                    |                                  |
| Chromaticity Coordinate X (Nom)    | 514                              |
| Chromaticity Coordinate Y (Nom)    | 424                              |
| Correlated Color Temperature (Nom) | 2100 K                           |
| Luminous Efficacy (Rated) (Min)    | 96 lm/W                          |
| Luminous Efficacy (rated) (Nom)    | 106 lm/W                         |
| Color rendering index (CRI)        | 17                               |
| Operating and Electrical           |                                  |
| Power Consumption                  | 150.6 W                          |
| Lamp Current (Nom)                 | 3.2 A                            |
| Voltage (Nom)                      | 55 V                             |
| Voltage (Nom)                      | 55 V                             |

| Mechanical and Housing          |                             |
|---------------------------------|-----------------------------|
| Bulb Finish                     | Clear                       |
| Bulb Material                   | Hard Glass                  |
| Bulb Shape                      | ED-23 1/2                   |
| Approval and Application        |                             |
| Mercury (Hg) Content (Max)      | 17 mg                       |
| Product Data                    |                             |
| Order product name              | SON 150W E39 ED75 CL SLV/12 |
| Full product name               | SON 150W E39 ED75 CL SLV/12 |
| Order code                      | 928601139701                |
| Material Nr. (12NC)             | 928601139701                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 046677368746                |
| Numerator - Packs per outer box | 12                          |
| EAN/UPC - Case                  | 50046677368741              |

Dimensional drawing

| Product                     |
|-----------------------------|
| SON 150W E39 ED75 CL SLV/12 |

