



Ceramalux ALTO

SON 70W E39 ED75 CL SLV/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)

Light Technical	
Chromaticity Coordinate X (Nom)	522
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	86 lm/W
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	13

Operating and Electrical	
Power Consumption	70.2 W
Lamp Current (Nom)	1.6 A
Voltage (Nom)	52 V
Voltage (Nom)	52 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2

Approval and Application	
Mercury (Hg) Content (Max)	17 mg

Product Data	
Order product name	SON 70W E39 ED75 CL SLV/12
Full product name	SON 70W E39 ED75 CL SLV/12
Order code	928601139901
Material Nr. (12NC)	928601139901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368692
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677368697

Ceramalux ALTO

Dimensional drawing

Product

SON 70W E39 ED75 CL SLV/12

