



Ceramalux Non-ALTO

C1000S52/ED37 6PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	517
Chromaticity Coordinate Y (Nom)	423
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	108 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	1,003 W
Lamp Current (Nom)	4.7 A
Voltage (Nom)	225 V
Voltage (Nom)	225 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED37
Approval and Application	
Mercury (Hg) Content (Max)	55.2 mg
Product Data	
Order product name	C1000S52/ED37 6PK
Full product name	C1000S52/ED37 6PK
Order code	323865
Material Nr. (12NC)	928601140701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677323868
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677323863

Ceramalux Non-ALTO

Dimensional drawing



Product	D	C (max)
C1000S52/ED37 6PK	120 mm	289 mm

