



Ceramalux Instant Restrike

C400S51/2 12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	418
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Nom)	47 mg
Product Data	
Order product name	37688-9 400W C400S51/2 Dual Arc Hp Lamp
Full product name	C400S51/2 12PK
Order code	376889
Material Nr. (12NC)	928601145401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677376888
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677376883

Ceramalux Instant Restrike

Dimensional drawing

Product	D	C (max)
37688-9 400W C400S51/2 Dual Arc Hp Lamp	2.25 inch	9.75 inch

