



Ceramalux Instant Restrike

C70S62/2 12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	523
Chromaticity Coordinate Y (Nom)	423
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	83.5 lm/W
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Lamp Current (Nom)	1.6 A
Voltage (Nom)	52 V
Voltage (Nom)	52 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Approval and Application	
Mercury (Hg) Content (Max)	34 mg
Product Data	
Order product name	C70S62/2 12PK
Full product name	C70S62/2 12PK
Order code	265413
Material Nr. (12NC)	928601145801
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677265410
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677265415

Ceramalux Instant Restrike

Dimensional drawing

Product	D	C (max)
C70S62/2 12PK	2.938 inch	7.75 inch

