



Ceramalux Non-ALTO

C150S55/M 3PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	514
Chromaticity Coordinate Y (Nom)	424
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	96 lm/W
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	17
Operating and Electrical	
Power Consumption	150.6 W
Lamp Current (Nom)	3.2 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Approval and Application	
Mercury (Hg) Content (Max)	17 mg
Product Data	
Order product name	150W BD17 HP SODIUM HID CLR
Full product name	C150S55/M 3PK
Order code	460832
Material Nr. (12NC)	928601147414
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677460839
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677460834

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
150W BD17 HP SODIUM HID CLR	55 mm	145 mm

