



Ceramalux ALTO Non-Cycling

C400S51/ALTO NC HPS 12PK

Philips Ceramalux High Pressure Sodium Non-Cycling Lamps are a better value than standard high pressure sodium lamps, with longer life and reduced maintenance cost.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® Non-Cycling
Light Technical	
Chromaticity Coordinate X (Nom)	0.524
Chromaticity Coordinate Y (Nom)	0.420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V

Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Nom)	3.4 mg
Product Data	
Order product name	C400S51/ALTO NC HPS 12PK
Full product name	C400S51/ALTO NC HPS 12PK
Order code	147439
Material Nr. (12NC)	928601156302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677147433

Ceramalux ALTO Non-Cycling

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677147438

Dimensional drawing



Product	D	L	C (max)
C400S51/ALTO NC HPS 12PK	2.25 inch	5.750 inch	9.75 inch

