



Pulse Start Metal Halide Protected

MP400/C/BU/PS 6PK

Philips Protected Pulse Start Metal Halide “O” Rated Lamps are a better alternative to the standard switch start metal halide.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	20,000 hour(s)

Light Technical	
Color Code	635 [CCT of 3500K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	420
Chromaticity Coordinate Y (Nom)	400
Correlated Color Temperature (Nom)	3600 K
Luminous Efficacy (Rated) (Min)	81 lm/W
Luminous Efficacy (rated) (Nom)	91 lm/W
Color rendering index (CRI)	68

Operating and Electrical	
Lamp Current (Nom)	3.25 A
Voltage (Nom)	135 V
Voltage (Nom)	135 V

Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	ED37

Approval and Application	
Mercury (Hg) Content (Max)	65 mg

Product Data	
Order product name	MP400/C/BU/PS 6PK
Full product name	MP400/C/BU/PS 6PK

Pulse Start Metal Halide Protected

Order code	928601158202
Material Nr. (12NC)	928601158202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677133351

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677133356

Dimensional drawing

Product	D	A (max)	B (max)	B (min)
MP400/C/BU/PS 6PK	4.625 inch	11.5 inch		

