



Pulse Start Metal Halide Standard

MS400/BU/ED28/PS 12PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Operating and Electrical	
Cap-Base	E39 [Single Contact Mogul Screw]	Lamp Current (Nom)	3.2 A
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Voltage (Nom)	135 V
Life to 50% Failures (Nom)	20,000 hour(s)	Voltage (Nom)	135 V
Light Technical		Mechanical and Housing	
Color Code	640 [CCT of 4000K]	Bulb Finish	Clear
Color Designation	Cool White (CW)	Bulb Material	Hard Glass
Chromaticity Coordinate X (Nom)	385	Bulb Shape	ED28
Chromaticity Coordinate Y (Nom)	390		
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (Rated) (Min)	105 lm/W	Mercury (Hg) Content (Nom)	50 mg
Luminous Efficacy (rated) (Nom)	110 lm/W		
Color rendering index (CRI)	68	Product Data	
		Order product name	PS MH Std 400W/640 CW Mog ED28 1SL
		Full product name	MS400/BU/ED28/PS 12PK

Pulse Start Metal Halide Standard

Order code	232520
Material Nr. (12NC)	928601165501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677232528

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677232523

Dimensional drawing



Product	D	C (max)
PS MH Std 400W/640 CW Mog ED28 1SL	3.5 inch	8.3 inch

