



# MasterColor CDM ED17 Standard

## MHC150/C/U/M/4K ALTO 12PK

Energy savings without changing a ballast!. A high-efficiency enclosed E-rated CDM lighting solution that provides energy savings without compromising light quality.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	940 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.368
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	90
Operating and Electrical	
Lamp Current (Nom)	1.8 A


Voltage (Nom)	95 V
Voltage (Nom)	95 V
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	BD17
Approval and Application	
Mercury (Hg) Content (Nom)	12.3 mg
Product Data	
Order product name	MHC150/C/U/M/4K ALTO 12PK
Full product name	MHC150/C/U/M/4K ALTO 12PK
Order code	377218
Material Nr. (12NC)	928601170201

MasterColor CDM ED17 Standard

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677377212
Numerator - Packs per outer box	12

EAN/UPC - Case	50046677377217
----------------	----------------

Dimensional drawing



Product	D	C (max)
MHC150/C/U/M/4K ALTO 12PK	2.125 inch	5.438 inch

