



# Energy Advantage CDM Lamps with Allstart Technology

## CDM260/U/O/4K ED28 EA AllStart

Philips Energy Advantage CDM lamps with AllStart Technology is a high-efficiency protected “O” rated CDM lighting solution that provides energy savings without compromising light quality.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	Energy Advantage AllStart
Life to 50% Failures (Nom)	20,000 hour(s)

Light Technical	
Color Code	940 [CCT of 4000K]
Color Designation	4000 Kelvin
Saturated Red (R9)	50
Chromaticity Coordinate X (Nom)	.381
Chromaticity Coordinate Y (Nom)	.384

Luminous Efficacy (Rated) (Min)	95 lm/W
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	90

Operating and Electrical	
Lamp Current (Nom)	2.43 A
Voltage (Nom)	130 V
Voltage (Nom)	130 V


Mechanical and Housing	
Bulb Finish	Clear

Energy Advantage CDM Lamps with Allstart Technology

Bulb Shape	ED28
Approval and Application	
Mercury (Hg) Content (Max)	31 mg
Product Data	
Order product name	CDM260/U/O/4K ED28 EA AllStart
Order code	928601174201


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601174201
Full product name	CDM260/U/O/4K ED28 EA AllStart
EAN/UPC - Case	50046677419375
EAN/UPC - Product/Case	046677419370

Dimensional drawing



Product	D	D	L (min)	L (max)	L	C
CDM260/U/O/4K ED28 EA AllStart	3.5 inch	88.9 mm	125 mm	129 mm	127 mm	8.375 inch


Photometric data



Spectral Power Distribution Colour - CDM260/U/O/4K ED28 EA AllStart

# Energy Advantage CDM Lamps with Allstart Technology

## Lifetime



Life Expectancy Diagram - CDM260/U/O/4K ED28 EA AllStart



Lumen Maintenance Diagram - CDM260/U/O/4K ED28 EA AllStart

