# **PHILIPS** Lighting



# MasterColor CDM ED17 Protected Elite 4200K

## MHC70/U/MP/4K ELITE

MasterColor Elite Protected Ceramic Metal Halide ED-17 4200K Lamps provide excellend lumen maintenance and outstanding performance over time in a protected lamp.

#### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope ot the lamp is broken or puntured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precuations are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- WARNING: The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rapture occur. The following operating instructions are recommended to minimize the occurrences.
- The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rapture occur. The following operating instructions are recommended to minimize the occurrences.
- RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.


#### **Product data**

### MasterColor CDM ED17 Protected Elite 4200K

General Information			
Cap-Base	E26 [Single Contact Medium Screw]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Features	ELITE		
Life to 50% Failures (Nom)	20,000 hour(s)		
Light Technical			
Color Code	940 [CCT of 4000K]		
Color Designation	Cool White (CW)		
Chromaticity Coordinate X (Nom)	0.441		
Chromaticity Coordinate Y (Nom)	0.392		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (Rated) (Min)	85 lm/W		
Luminous Efficacy (rated) (Nom)	92 lm/W		
Color rendering index (CRI)	90		
Operating and Electrical			
Power Consumption	70.4 W		
Lamp Current (Nom)	0.9 A		
Voltage (Nom)	100 V		
Voltage (Nom)	100 V		

Mechanical and Housing		
Bulb Finish	Clear	
Bulb Material	Hard Glass	
Bulb Shape	ED17P [ED-17P Protected]	
Approval and Application		
Mercury (Hg) Content (Max)	7.1 mg	
Product Data		
Order product name	MHC70/U/MP/4K ELITE	
Full product name	MHC70/U/MP/4K ELITE	
Order code	928601177901	
Material Nr. (12NC)	928601177901	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677429959	
Numerator - Packs per outer box	12	
EAN/UPC - Case	50046677429954	

#### Dimensional drawing



Product	D	C (max)
MHC70/U/MP/4K ELITE	2.125 inch	5.438 inch



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.