



Essential LEDspot MR16

Essential LED 2.6–20W 2700K MR16 24D

Essential LEDspots MR16 are compatible with most existing fixtures with a GU5.3 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots MR16 deliver significant energy savings and minimize initial investment.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	24 degree(s)
Luminous Flux	135 lm
Luminous Intensity (Nom)	460 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	51.92 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	2.6 W
Lamp Current (Nom)	363 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.5
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh


Product Data	
Order product name	Essential LED 2.6–20W 2700K MR16 24D

Essential LEDspot MR16

Full product name	Essential LED 2.6-20W 2700K MR16 24D
Full product code	871829166354600
Order code	929000232708
Material Nr. (12NC)	929000232708
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718291663546
Numerator - Packs per outer box	20
EAN/UPC - Case	8718291663553

Dimensional drawing



Product	D	C
Essential LED 2.6-20W 2700K MR16 24D	49.9 mm	47.6 mm

Photometric data



Light Distribution Diagram - Essential LED 2.6-20W 2700K MR16 24D

