



MASTER VALUE LEDs pot LV

MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D

Philips MASTER VALUE MR16 is the series of Low Voltage (12VAC) Halogen MR16 replacements. Not only does it employ Philips' patented solution to guarantee the broadest possible compatibility with standard 12V Halogen electronic transformers. It also delivers beam intensity which is equivalent to the 50W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact form with Halogen lamps.)

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	24 degree(s)
Luminous Flux	440 lm
Luminous Intensity (Nom)	2,200 cd
Color Designation	White (WH)


Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	62.86 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	415 lm

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	715 mA
Starting Time (Nom)	0.5 s


MASTER VALUE LEDspot LV

Warm-up time to 60% light	instant full light s
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	110 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

Dimensional drawing




Photometric data



Light Distribution Diagram - MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D

Product Data	
Order product name	MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D
Full product name	MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D
Full product code	871829165449000
Order code	929000237402
Material Nr. (12NC)	929000237402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291654490
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291654506

Product	D	C
MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D	54 mm	50 mm



Spectral Power Distribution Colour - MAS LEDspotLV D 7-35W GU5.3 830 MR16 24D

MASTER VALUE LEDspot LV

