



# MASTER LEDspot PAR

## MAS LEDspot D 9.5-75W 840 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

### Product data


General Information		Power Consumption	
Cap-Base	E27 [E27]	Power Consumption	9.5 W
Nominal lifetime	40,000 hour(s)	Lamp Current (Nom)	46 mA
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	instant full light s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.9
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Beam Angle (Nom)	25 degree(s)		
Luminous Flux	750 lm	Mechanical and Housing	
Luminous Intensity (Nom)	3,850 cd	Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	78.95 lm/W	Suitable For Accent Lighting	Yes
Color Consistency	<6	Energy Consumption kWh/1000 h	10 kWh
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Luminous Flux in 90° Cone (Rated)	750 lm	Order product name	MAS LEDspot D 9.5-75W 840 PAR30S 25D
		Full product name	MAS LEDspot D 9.5-75W 840 PAR30S 25D
		Full product code	871829171436100
		Order code	929000259002
		Material Nr. (12NC)	929000259002
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

# MASTER LEDspot PAR

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291714361
Numerator - Packs per outer box	10


EAN/UPC - Case	8718291714378
----------------	---------------

## Dimensional drawing



Product	D	C
MAS LEDspot D 9.5-75W 840 PAR30S 25D	92 mm	94.1 mm

## Photometric data



### Light Distribution Diagram - MAS LEDspot D 9.5-75W 840 PAR30S 25D

