



# CorePro Plastic LEDcandles & lusters

## CorePro luster ND 6-40W E14 827 P48 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 Hz
Input Frequency	50 Hz

Power Consumption	6 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P48 [P 48mm]


Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh

CorePro Plastic LEDcandles & lusters

Product Data	
Order product name	CorePro luster ND 6-40W E14 827 P48 FR
Full product name	CorePro luster ND 6-40W E14 827 P48 FR
Full product code	871829176240900
Order code	929000273302
Material Nr. (12NC)	929000273302


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291762409
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291762416

Dimensional drawing




Product	D	C
CorePro luster ND 6-40W E14 827 P48 FR	48 mm	95 mm

Photometric data



Light Distribution Diagram - CorePro luster ND 6-40W E14 827 P48 FR



Spectral Power Distribution Colour - CorePro luster ND 6-40W E14 827 P48 FR

