



CorePro Plastic LEDcandles & lusters

CorePro luster ND 6-40W E14 827 P48 FR

The CorePro LEDcandles and lusters are designed for retrofit replacement of incandescent lamps and are particularly attractive for chandeliers. They are compatible with fixtures with an E14 holder for candles and E14 or E27 holders for lusters and are available in multiple color temperatures. LED lamps deliver huge energy savings of up to 80% energy-saving compared with halogen lamps and provide excellent quality of light. By offering a lifetime of 15,000 hours it lowers maintenance costs. The CorePro LED candles and lusters are perfect for your basic lighting needs.

Product data


General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Line Frequency	50 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 Hz
Switching Cycle	50,000	Power Consumption	6 W
Lighting Technology	LED	Lamp Current (Nom)	35 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	827 [CCT of 2700K]	Warm-up time to 60% light	instant full light s
Luminous Flux	470 lm	Power Factor (Fraction)	0.4
Color Designation	Warm White (WW)	Voltage (Nom)	220-240 V
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	78 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %		

CorePro Plastic LEDcandles & lusters

Bulb Shape	P48 [P 48mm]
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh
Product Data	
Order product name	CorePro luster ND 6-40W E14 827 P48 FR
Full product name	CorePro luster ND 6-40W E14 827 P48 FR


Full product code	871829176240900
Order code	929000273302
Material Nr. (12NC)	929000273302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291762409
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291762416

Dimensional drawing




Product	D	C
CorePro luster ND 6-40W E14 827 P48 FR	48 mm	95 mm

Photometric data



Light Distribution Diagram - CorePro luster ND 6-40W E14 827 P48 FR



Spectral Power Distribution Colour - CorePro luster ND 6-40W E14 827 P48 FR

