



# Fortimo LED linear light module

## Cable Fortimo 7PA to 6wire - 600mm

The Fortimo LED linear light module (LLM) system represents a breakthrough in energy-efficient LED lighting for urban and residential applications. Cutting-edge LED technology ensures peak performance, delivering energy savings with Constant Light Output without compromising on light quality and comfort. Fortimo LED LLM offers a diffused white light LED alternative to traditional frosted light sources such as (compact) fluorescent, high-pressure mercury (HPL) and high-pressure sodium (SON) lamps. Designed primarily for residential outdoor lighting applications, this reliable, upgradeable solution is also suitable for many professional indoor applications. Fortimo LED LLM is a Green Product, contains no mercury and is fully RoHS-compliant.


### Product data

| General Information    |                                    |
|------------------------|------------------------------------|
| Lighting Technology    | LED                                |
| Mechanical and Housing |                                    |
| Product Length         | 600 mm                             |
| Product Data           |                                    |
| Order product name     | Cable Fortimo 7PA to 6wire - 600mm |
| Full product name      | Cable Fortimo 7PA to 6wire - 600mm |

|                                 |                 |
|---------------------------------|-----------------|
| Full product code               | 871829121412000 |
| Order code                      | 929000803903    |
| Material Nr. (12NC)             | 929000803903    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8718291214120   |
| Numerator - Packs per outer box | 10              |
| EAN/UPC - Case                  | 8718291214137   |

Fortimo LED linear light module

Dimensional drawing



| Product                            | A1     |
|------------------------------------|--------|
| Cable Fortimo 7PA to 6wire - 600mm | 600 mm |

