



LED PAR30 S/L

12PAR30S/S15 3000 CW SO-B 6/1

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	15 degree(s)
Luminous Flux	780 lm
Luminous Intensity (Nom)	6,300 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	62.40 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12.5 W
Lamp Current (Nom)	115 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Order product name	120V PAR30S 12.5W 15D 3000K 780 CW SOB
Full product name	12PAR30S/S15 3000 CW SO-B 6/1
Order code	434936
Material Nr. (12NC)	929001110104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677434939
Numerator - Packs per outer box	6

LED PAR30 S/L


EAN/UPC - Case	50046677434934
----------------	----------------

Dimensional drawing



Product	D	C
120V PAR30S 12.5W 15D 3000K 780 CW SOB	92 mm	93 mm

Photometric data



Light Distribution Diagram - 120V PAR30S 12.5W 15D 3000K 780 CW SOB

