



LED PAR30 S/L

120V PAR30S 12W 25D 2700K 900 D AF SO

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.


Product data

General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	25,000 hour(s)	Power Factor (Fraction)		0.85
Switching Cycle	50,000	Voltage (Nom)		120 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	T-Case Maximum (Nom)		89 °C
Light Technical		Controls and Dimming		
Color Code	827 [CCT of 2700K]	Dimmable		Yes
Beam Angle (Nom)	25 degree(s)	Mechanical and Housing		
Luminous Flux	850 lm	Bulb Shape		PAR30S [PAR 3.75 inch/95mm Short]
Luminous Intensity (Nom)	5,000 cd	Approval and Application		
Color Designation	Warm White (WW)	Suitable For Accent Lighting		Yes
Correlated Color Temperature (Nom)	2700 K	Energy Certifications		Energy Star
Luminous Efficacy (rated) (Nom)	71 lm/W	Product Data		
Color Consistency	<6	Order product name		120V PAR30S 12W 25D 2700K 900 D AF SO
Color rendering index (CRI)	80	Full product name		120V PAR30S 12W 25D 2700K 900 D AF SO
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order code		929001112504
Operating and Electrical		Material Nr. (12NC)		929001112504
Line Frequency	60 Hz	Numerator - Quantity Per Pack		1
Input Frequency	60 Hz			
Power Consumption	12 W			
Lamp Current (Nom)	121 mA			

LED PAR30 S/L



EAN/UPC - Product/Case	046677435295
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677435290

Dimensional drawing




Product	D	C
120V PAR30S 12W 25D 2700K 900 D AF SO	92 mm	92.7 mm

Photometric data



Spectral Power Distribution Colour - 120V PAR30S 12W 25D 2700K 900 D AF SO

Light Distribution Diagram - 120V PAR30S 12W 25D 2700K 900 D AF SO



Access Lighting - Spain

General uniform lighting - 120V PAR30S 12W 25D 2700K 900 D AF SO

LED PAR30 S/L

