



LED PAR30 S/L

120V PAR30S 12W 25D 4000K 900 D AF SO

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	950 lm
Luminous Intensity (Nom)	5,500 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12 W
Lamp Current (Nom)	121 mA

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.85
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	89 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Certifications	Energy Star
Product Data	
Order product name	120V PAR30S 12W 25D 4000K 900 D AF SO
Full product name	120V PAR30S 12W 25D 4000K 900 D AF SO
Order code	929001112704
Material Nr. (12NC)	929001112704
Numerator - Quantity Per Pack	1

LED PAR30 S/L


EAN/UPC - Product/Case	046677435318
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677435313

Dimensional drawing




Product	D	C
120V PAR30S 12W 25D 4000K 900 D AF SO	92 mm	92.7 mm


Photometric data



Spectral Power Distribution Colour - 120V PAR30S 12W 25D 4000K 900 D AF SO



Light Distribution Diagram - 120V PAR30S 12W 25D 4000K 900 D AF SO



Accent Lighting - Spots

General uniform lighting - 120V PAR30S 12W 25D 4000K 900 D AF SO

LED PAR30 S/L

