



MASTER VALUE LEDspot MV

LED 60W E27 WW 230V R63 36D DIM SRT4

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information			
Cap-Base	E27 [E27]	Luminous Intensity (Nom)	600 cd
Nominal lifetime	15,000 hour(s)	Color Designation	Warm White (WW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	2700 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	60.53 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
Light Technical		Color rendering index (CRI)	80
Color Code	827 [CCT of 2700K]	LLMF At End Of Nominal Lifetime (Nom)	70 %
Beam Angle (Nom)	36 degree(s)	Luminous Flux in 90° Cone (Rated)	345 lm
Luminous Flux	345 lm	Operating and Electrical	
		Line Frequency	50 to 60 Hz

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	5.7 W
Lamp Current (Nom)	29 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220–240 V

Temperature

T-Case Maximum (Nom)	82 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	R63 [R 63mm]
------------	--------------


Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	6 kWh

Product Data



Order product name	LED 60W E27 WW 230V R63 36D DIM SRT4
Full product name	LED 60W E27 WW 230V R63 36D DIM SRT4
Full product code	871829178541501
Order code	929001114458
Material Nr. (12NC)	929001114458
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291785415
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696729984

Dimensional drawing



Product	D	C
LED 60W E27 WW 230V R63 36D DIM SRT4	63 mm	102 mm

Photometric data




Spectral Power Distribution Colour - LED 60W E27 WW 230V R63 36D DIM SRT4

General uniform lighting - LED 60W E27 WW 230V R63 36D DIM SRT4

MASTER VALUE LEDspot MV

Photometric data



Light Distribution Diagram - LED 60W E27 WW 230V R63 36D DIM SRT4

