



MASTER VALUE LEDspot LV

MAS LEDspotLV 3.5-20W 827 MR11 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU4 [GU4]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	24 degree(s)

MASTER VALUE LEDspot LV

Luminous Flux	210 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	200 lm

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.5
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	94 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	MR11 [1.375inch/35mm]
------------	-----------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

Product Data

Order product name	MAS LEDspotLV 3.5-20W 827 MR11 24D
Full product name	MAS LEDspotLV 3.5-20W 827 MR11 24D
Full product code	871869641019600
Order code	929001123802
Material Nr. (12NC)	929001123802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696410196
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696410202


Dimensional drawing




Product	D	C
MAS LEDspotLV 3.5-20W 827 MR11 24D	35 mm	40 mm

MASTER VALUE LEDspot LV

Photometric data



Light Distribution Diagram - MAS LEDspotLV 3.5-20W 827 MR11 24D



Spectral Power Distribution Colour - MAS LEDspotLV 3.5-20W 827 MR11 24D

