



LED InstantFit Lamps

12T8/48-3500 IF 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Warnings and Safety

- Philips LED T8 InstantFit lamps will only operate properly on compatible instant-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit www.philips.com/tled

Product data


General Information		Warm-up time to 60% light	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Factor (Fraction)	0.9
Nominal lifetime	50,000 hour(s)	Voltage (Nom)	120-277 V
Switching Cycle	50,000	Temperature	
Lighting Technology	LED	Ambient temperature range	-20 °C to 45 °C
EU RoHS compliant	Yes	T-Case Maximum (Nom)	40 °C
Light Technical		Controls and Dimming	
Color Code	835 [CCT of 3500K]	Dimmable	No
Beam Angle (Nom)	160 degree(s)	Mechanical and Housing	
Luminous Flux	1,500 lm	Product Length	1,200 mm
Correlated Color Temperature (Nom)	3500 K	Approval and Application	
Color Consistency	<6	Energy Saving Product	Yes
Color rendering index (CRI)	82	Approval Marks	UL certificate RoHS compliance KEMA Keur certificate DLC compliance
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	14.5 kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Power Consumption	12 W		
Starting Time (Nom)	0.5 s		

LED InstantFit Lamps

Product Data	
Order product name	12T8/48-3500 IF 10/1
Full product name	12T8/48-3500 IF 10/1
Order code	929001124004
Material Nr. (12NC)	929001124004
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	046677453596
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677453591

Dimensional drawing




Product	D1	D2	A1	A2	A3
12T8/48-3500 IF 10/1	25.68 mm	28 mm	1,198.0 mm	1,205.0 mm	1,212.0 mm

Photometric data



Spectral Power Distribution Colour - 12T8/48-3500 IF 10/1

General uniform lighting - 12T8/48-3500 IF 10/1



Light Distribution Diagram - 12T8/48-3500 IF 10/1

LED InstantFit Lamps

