



MASTER LEDtube EM/ Mains T8

MAS LEDtube 1200mm HO 16W840 T8 RS

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

• –

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,100 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	16 W
Lamp Current (Max)	77 mA
Lamp Current (Min)	68 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No

MASTER LEDtube EM/Mains T8

Mechanical and Housing	
Product Length	1,200 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
Product Data	
Order product name	MAS LEDtube 1200mm HO 16W840 T8 RS


Full product name	MAS LEDtube 1200mm HO 16W840 T8 RS
Full product code	871869642200700
Order code	929001126202
Material Nr. (12NC)	929001126202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696422007
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696422014

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HO 16W840 T8 RS	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data



Light Distribution Diagram - MAS LEDtube 1200mm HO 16W840 T8 RS



Spectral Power Distribution Colour - MAS LEDtube 1200mm HO 16W840 T8 RS

MASTER LEDtube EM/Mains T8

