



Essential LEDtube

ESSENTIAL LEDtube 1200mm 18W840 T8 AP I

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

产品数据


一般信息		电压 (标称)	
底盖	G13 [Medium Bi-Pin Fluorescent]	220-240 V	
标称使用寿命	30,000 小时	温度	
切换循环	50,000	环境温度范围	-20 °C 至 45 °C
照明技术	LED	最大外壳温度 (标称)	53 °C
符合欧盟 RoHS 规范	是	控制和调光	
灯技术		可调光	否
颜色代码	840 [CCT of 4000K]	机械和外壳	
光束角度 (标称)	150 °	产品长度	1,200 mm
光通量	1,600 lm	审批和申请	
相关色温 (标称)	4000 K	节能产品	是
颜色一致性	<6	适用于重点照明	否
显色指数 (CRI)	80	批准标志	CE 标志 遵从 RoHS KEMA Keur 证书
标称使用寿命结束时灯的光通维持率 (标称)	70 %	能耗 kWh/1000 h	18 kWh
操作和电气		产品数据	
纹频率	50 to 60 Hz	订单产品名称	ESSENTIAL LEDtube 1200mm 18W840 T8 AP I
输入频率	50 至 60 Hz	完整的产品名称	ESSENTIAL LEDtube 1200mm 18W840 T8 AP I
功耗	18 W	完整产品代码	871869642520600
启动时间 (标称)	0.5 s	订购代码	929001128208
60% 灯光下的预热时间	即亮 s		
功率系数 (小数)	0.9		

Essential LEDtube

材料编号 (12NC)	929001128208
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696425206
计算器 - 每个外包装箱中的包数	10



EAN/UPC - 案例	8718696425213
--------------	---------------

二维绘图



Product	D1	D2	A1	A2	A3
ESSENTIAL LEDtube 1200mm 18W840 T8 AP I	25.68 mm	28 mm	1,198.0 mm	1,205.0 mm	1,212.0 mm

光度数据



Light Distribution Diagram - ESSENTIAL LEDtube 1200mm 18W840 T8 AP I

Spectral Power Distribution Colour - ESSENTIAL LEDtube 1200mm 18W840 T8 AP I

