



# MASTER VALUE LEDspot MV

## MAS LEDspotMV VLE D 3.5-35W GU10 830 25D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information			
Cap-Base	GU10 [GU10]	Luminous Intensity (Nom)	1,000 cd
Nominal lifetime	35,000 hour(s)	Color Designation	Warm White (WW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	3000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	77.14 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	270 lm
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	25 degree(s)		
Luminous Flux	290 lm		

# MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	20 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	79 °C
----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------

## Approval and Application


Suitable For Accent Lighting	Yes
------------------------------	-----

Energy Consumption kWh/1000 h	4 kWh
-------------------------------	-------

## Product Data


Order product name	MAS LEDspotMV VLE D 3.5-35W GU10 830 25D
Full product name	MAS LEDspotMV VLE D 3.5-35W GU10 830 25D
Full product code	871869643834300
Order code	929001129902
Material Nr. (12NC)	929001129902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696438343
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696438350

## Dimensional drawing




Product	D	C
MAS LEDspotMV VLE D 3.5-35W GU10 830 25D	50 mm	55 mm

## Photometric data



Light Distribution Diagram - MAS LEDspotMV VLE D 3.5-35W GU10 830 25D



Spectral Power Distribution Colour - MAS LEDspotMV VLE D 3.5-35W GU10 830 25D

## MASTER VALUE LEDspot MV

