



MASTER VALUE LEDspot MV

MASTER LEDspotMV VLE D 4.3-50W GU10 840 25D

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information		Light Technical	
Cap-Base	GU10 [GU10]	Color Code	840 [CCT of 4000K]
Nominal lifetime	35,000 hour(s)	Beam Angle (Nom)	25 degree(s)
Switching Cycle	50,000	Luminous Flux	420 lm
Lighting Technology	LED	Luminous Intensity (Nom)	1,400 cd
EU RoHS compliant	Yes	Color Designation	White (WH)
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	90.70 lm/W

MASTER VALUE LEDspot MV

Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	390 lm

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp Current (Nom)	23 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	181 °F
----------------------	--------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes

Product Data

Order product name	MAS LEDspotMV VLE D 4.3-50W GU10 840 25D
Full product name	MASTER LEDspotMV VLE D 4.3-50W GU10 840 25D
Full product code	871869643846600
Order code	304733
Material Nr. (12NC)	929001130302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696438466
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696438473


Dimensional drawing




Product	D	C
MAS LEDspotMV VLE D 4.3-50W GU10 840 25D	2 inch	2-3/16 inch

MASTER VALUE LEDspot MV

Photometric data



Light Distribution Diagram - MAS LEDspotMV VLE D 4.3-50W GU10 840 25D



Spectral Power Distribution Colour - MAS LEDspotMV VLE D 4.3-50W GU10 840 25D

