



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2-20W 830 G4

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs without any compromise on light quality.

Product data


General Information			
Cap-Base	G4 [G4]	Power Consumption	2 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	290 mA
Switching Cycle	50,000	Wattage Equivalent	20 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	12 V
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Luminous Flux	200 lm		
Color Designation	White (WH)	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Shape	Capsule
Luminous Efficacy (rated) (Nom)	100 lm/W		
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h	3 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Product Data	
Line Frequency	50 to 60 Hz	Order product name	CorePro LEDcapsuleLV 2-20W 830 G4
Input Frequency	50 to 60 Hz	Full product name	CorePro LEDcapsuleLV 2-20W 830 G4

CorePro LEDcapsule LV

Full product code	871869641916800
Order code	41916800
Material Nr. (12NC)	929001131802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696419168



Numerator - Packs per outer box	12
EAN/UPC - Case	8718696419175

Dimensional drawing



Product	D	C
CorePro LEDcapsuleLV 2-20W 830 G4	14.3 mm	45 mm

Photometric data



Light Distribution Diagram - CorePro LEDcapsuleLV 2-20W 830 G4

Spectral Power Distribution Colour - CorePro LEDcapsuleLV 2-20W 830 G4

