



MASTER VALUE LEDs

pot LV

MASTER LED 5.5-50W 3000K MR16 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information		EU RoHS compliant	
Cap-Base	GU5.3 [GU5.3]	Yes	
Nominal lifetime	25,000 hour(s)	Light Technical	
Switching Cycle	50,000	Color Code	830 [CCT of 3000K]
Lighting Technology	LED	Beam Angle (Nom)	24 degree(s)

MASTER VALUE LEDspot LV

Luminous Flux	425 lm
Luminous Intensity (Nom)	1,800 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	77.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	5.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------


Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	MASTER LED 5.5-50W 3000K MR16 24D
Full product name	MASTER LED 5.5-50W 3000K MR16 24D
Full product code	871869647607900
Order code	929001146708
Material Nr. (12NC)	929001146708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476079
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476086



Dimensional drawing



Product	D	C
MASTER LED 5.5-50W 3000K MR16 24D	50.2 mm	49 mm

MASTER VALUE LEDspot LV

Photometric data



General uniform lighting - MASTER LED 5.5-50W 3000K MR16 24D

Light Distribution Diagram - MASTER LED 5.5-50W 3000K MR16 24D

