



MASTER VALUE LEDs

pot LV

MASTER LED 4-35W 2700K MR16 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information			
Cap-Base	GU5.3 [GU5.3]	Beam Angle (Nom)	24 degree(s)
Nominal lifetime	25,000 hour(s)	Luminous Flux	240 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	1,000 cd
Lighting Technology	LED	Color Designation	Warm White (WW)
EU RoHS compliant	Yes	Correlated Color Temperature (Nom)	2700 K
		Luminous Efficacy (rated) (Nom)	65.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	827 [CCT of 2700K]		

MASTER VALUE LEDspot LV

Luminous Flux in 90° Cone (Rated)	220 lm
-----------------------------------	--------

Operating and Electrical

Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	4 W
Lamp Current (Nom)	520 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

Product Data


Order product name	MASTER LED 4-35W 2700K MR16 24D
Full product name	MASTER LED 4-35W 2700K MR16 24D
Full product code	871869647619200
Order code	929001147408
Material Nr. (12NC)	929001147408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476192
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476208

Dimensional drawing



Product	D	C
MASTER LED 4-35W 2700K MR16 24D	50 mm	49 mm

Photometric data



Light Distribution Diagram - MASTER LED 4-35W 2700K MR16 24D

Spectral Power Distribution Colour - MASTER LED 4-35W 2700K MR16 24D

MASTER VALUE LEDspot LV

