



# MASTER LEDtube EM/ Mains

## MASTER LEDtube 1500mm UO 25W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

### Warnings and Safety

• -

### Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	865 [CCT of 6500K]
Beam angle (nom.)	160 degree(s)
Luminous Flux	3,700 lm
Correlated Colour Temperature	6500 K
Luminous efficacy (rated) (nom.)	148 lm/W
Colour consistency	<6
Colour rendering index (CRI)	83
LLMF at end of nominal lifetime (nom.)	70 %


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	25 W
Lamp current (max.)	113 mA
Lamp current (min.)	105 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.1 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20°C to 35°C
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	No

MASTER LEDtube EM/Mains

Mechanical and Housing	
Product length	1,500 mm
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Approval marks	CE marking KEMA Keur certificate RoHS compliance
Energy consumption kWh/1,000 hours	25 kWh
Product Data	
Order product name	MAS LEDtube 1500mm UO 25W 865 T8


Full product name	MASTER LEDtube 1500mm UO 25W 865 T8
Full EOC	871869646163100
Order code	46163100
Material no. (12 NC)	929001149302
Local order code	MLEDTUBE15UO65R
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696461631
Numerator – packs per outer box	10
EAN/UPC – Case	8718696461648

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm UO 25W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm

Photometric data



Light Distribution Diagram – MAS LEDtube 1500mm UO 25W 865 T8



Spectral Power Distribution Colour – MAS LEDtube 1500mm UO 25W 865 T8

## MASTER LEDtube EM/Mains

