



# MASTER LEDspot LV

## MAS LEDspotLV D 8.0-50W 827 MR16 36D

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.


### Product data

General Information			
Cap-Base	GU5.3 [GU5.3]	Correlated Color Temperature (Nom)	2700 K
Nominal lifetime	40,000 hour(s)	Luminous Efficacy (rated) (Nom)	78 lm/W
Switching Cycle	50,000	Color Consistency	<6
Lighting Technology	LED	Color rendering index (CRI)	80
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	621 lm
Light Technical		Operating and Electrical	
Color Code	827 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	635 lm	Power Consumption	8 W
Luminous Intensity (Nom)	1,650 cd	Lamp Current (Nom)	900 mA
Color Designation	Warm White (WW)	Wattage Equivalent	50 W


# MASTER LEDspot LV

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
<b>Temperature</b>	
T-Case Maximum (Nom)	105 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Mechanical and Housing</b>	
Bulb Shape	MR16 [2inch/50mm]
<b>Approval and Application</b>	
Suitable For Accent Lighting	Yes

## Dimensional drawing



## Photometric data



Light Distribution Diagram - MAS LEDspotLV D 8.0-50W 827 MR16 36D

Energy Consumption kWh/1000 h	9 kWh
<b>Product Data</b>	
Order product name	MAS LEDspotLV D 8.0-50W 827 MR16 36D
Full product name	MAS LEDspotLV D 8.0-50W 827 MR16 36D
Full product code	871869651536500
Order code	929001150102
Material Nr. (12NC)	929001150102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696515365
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696515372

Product	D	C
MAS LEDspotLV D 8.0-50W 827 MR16 36D	51 mm	55 mm



Spectral Power Distribution Colour - MAS LEDspotLV D 8.0-50W 827 MR16 36D

## MASTER LEDspot LV

