



MR16/GU10/PAR16

8.5MRX16/F35 2700 DIM AF 10/1

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatability allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	35 degree(s)
Luminous Flux	635 lm
Luminous Intensity (Nom)	1,650 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	621 lm
Operating and Electrical	
Line Frequency	60 Hz

Input Frequency	60 Hz
Power Consumption	8.5 W
Lamp Current (Nom)	900 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	105 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	9 kWh

MR16/GU10/PAR16


Energy Certifications	Energy Star
Product Data	
Order product name	8.5MRX16/F35 2700 DIM AF 10/1
Full product name	8.5MRX16/F35 2700 DIM AF 10/1
Order code	929001150104
Material Nr. (12NC)	929001150104

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677457532
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677457537

Dimensional drawing

Product	D	C
8.5MRX16/F35 2700 DIM AF 10/1	51 mm	55 mm

Photometric data



Light Distribution Diagram – 8.5MRX16/F35 2700 DIM AF 10/1

Spectral Power Distribution Colour – 8.5MRX16/F35 2700 DIM AF 10/1

