



# LED InstantFit Lamps

## 17T8/48-4000 IFG 10/1

Philips InstantFit LED Lamp, 4ft. Glass (17W / 2100 lm / 4000K)

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

### Warnings and Safety

- Perform a visual inspection to ensure lamp holders (or sockets) are not damaged or loose. If the lamp holders (or sockets) are damaged, corroded, charred, blackened or loose, contact a qualified electrician for proper replacement.
- Please refer to the ballast compatibility guide located at [www.philips.com/instantfit](http://www.philips.com/instantfit).

### Product data


General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	50 to 60 Hz
Nominal lifetime	36,000 hour(s)	Lamp Current (Max)	17 W
Switching Cycle	50,000	Lamp Current (Min)	335 mA
Lighting Technology	LED	Starting Time (Nom)	145 mA
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	Instant full light s
Color Code	840 [CCT of 4000K]	Voltage (Nom)	0.9
Beam Angle (Nom)	240 degree(s)	Temperature	
Luminous Flux	2,100 lm	Ambient temperature range	-4 °F to 95 °F
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	140 °F
Color Consistency	<6	Controls and Dimming	
Color rendering index (CRI)	82	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

LED InstantFit Lamps

Mechanical and Housing	
Product Length	1,200 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	CE marking UL certificate RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	17T8/48-4000 IFG 10/1

Full product name	17T8/48-4000 IFG 10/1
Order code	456566
Material Nr. (12NC)	929001151104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677456566
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677456561

Dimensional drawing



Product	D1	D2	A1	A2	A3
17T8/48-4000 IFG 10/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data



## LED InstantFit Lamps

