



MASTER VALUE LEDs

pot LV

MASTER LED 7-50W 827 MR16 36D Dim

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)

MASTER VALUE LEDspot LV

Luminous Flux	420 lm
Luminous Intensity (Nom)	1,150 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	57.14 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	400 lm

Operating and Electrical

Power Consumption	7 W
Lamp Current (Nom)	720 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	92 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	MR16 [2inch/50mm]
------------	-------------------


Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

Product Data

Order product name	MASTER LED 7-50W 827 MR16 36D Dim
Full product name	MASTER LED 7-50W 827 MR16 36D Dim
Full product code	871869648963500
Order code	929001153108
Material Nr. (12NC)	929001153108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696489635
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696489642


Dimensional drawing




Product	D	C
MASTER LED 7-50W 827 MR16 36D Dim	51 mm	51 mm

MASTER VALUE LEDspot LV


Photometric data



Spectral Power Distribution Colour - MASTER LED 7-50W 827 MR16 36D Dim



Light Distribution Diagram - MASTER LED 7-50W 827 MR16 36D Dim



General uniform lighting - MASTER LED 7-50W 827 MR16 36D Dim

