



MR16/GU10/PAR16

7MR16/LED/F35/840/DIM AF2 10/1

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatability allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	35 degree(s)
Luminous Flux	530 lm
Luminous Intensity (Nom)	1,400 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	530 lm
Operating and Electrical	
Power Consumption	7 W


Lamp Current (Nom)	720 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	197.6 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh
Energy Certifications	Energy Star

MR16/GU10/PAR16

Product Data	
Order product name	7MR16/LED/F35/840/DIM AF2 10/1
Full product name	7MR16/LED/F35/840/DIM AF2 10/1
Order code	461608
Material Nr. (12NC)	929001153334
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	046677461607
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677461602

Dimensional drawing



Product	D	C
7MR16/LED/F35/840/DIM AF2 10/1	51 mm	51 mm

Photometric data



General Lighting - Beam

Light Distribution Diagram - 7MR16/LED/F35/840/DIM AF2 10/1



General uniform lighting - 7MR16/LED/F35/840/DIM AF2 10/1

Spectral Power Distribution Colour - 7MR16/LED/F35/840/DIM AF2 10/1

