



SceneSwitch LEDbulbs

Scene Switch A60 9.5-60W E27 3000K/6500K

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LEDbulbs, you can have different light settings from just one bulb. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	100,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865/830 [CCT of 6500K/3000K]
Luminous Flux	806 lm
Luminous Efficacy (rated) (Nom)	84.84 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Power Consumption	9.5 W
Lamp Current (Nom)	100 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s


Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	9.5 kWh
Product Data	
Order product name	Scene Switch A60 9.5-60W E27 3000K/ 6500K
Full product name	Scene Switch A60 9.5-60W E27 3000K/ 6500K

SceneSwitch LEDbulbs

Full product code	871869648550700
Order code	929001155919
Material Nr. (12NC)	929001155919
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696490846


Numerator - Packs per outer box	6
EAN/UPC - Case	8718696485514

Dimensional drawing




Product	D	C
Scene Switch A60 9.5-60W E27 3000K/6500K	61 mm	111 mm


Photometric data




Spectral Power Distribution Colour - Scene Switch A60 9.5-60W E27 3000K/6500K



Spectral Power Distribution Colour - Scene Switch A60 9.5-60W E27 3000K/6500K



General uniform lighting - Scene Switch A60 9.5-60W E27 3000K/6500K



Light Distribution Diagram - Scene Switch A60 9.5-60W E27 3000K/6500K

SceneSwitch LEDbulbs

