



# MasterClass LEDtube InstantFit T8

## 15T8/48-5000 IF 10/1 TAA

The MasterClass InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using the existing ballast. MasterClass TLEDs feature a shatter-resistant polycarbonate construction, 70,000 hour life and a standard 7-year limited warranty. When maximum energy savings and long life are needed, Philips MasterClass TLED are the solution.

### Product data

| General Information                   |                                 |
|---------------------------------------|---------------------------------|
| Cap-Base                              | G13 [Medium Bi-Pin Fluorescent] |
| Nominal lifetime                      | 40,000 hour(s)                  |
| Switching Cycle                       | 50,000                          |
| Lighting Technology                   | LED                             |
| EU RoHS compliant                     | Yes                             |
| Light Technical                       |                                 |
| Color Code                            | 850 [CCT of 5000K]              |
| Beam Angle (Nom)                      | 160 degree(s)                   |
| Luminous Flux                         | 2,100 lm                        |
| Correlated Color Temperature (Nom)    | 5000 K                          |
| Color Consistency                     | <6                              |
| Color rendering index (CRI)           | 82                              |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %                            |
| Operating and Electrical              |                                 |
| Line Frequency                        | 50 to 60 Hz                     |
| Input Frequency                       | 50 to 60 Hz                     |
| Power Consumption                     | 15 W                            |


| Lamp Current (Max)           | 290 mA               |
|------------------------------|----------------------|
| Lamp Current (Min)           | 110 mA               |
| Starting Time (Nom)          | 0.5 s                |
| Warm-up time to 60% light    | Instant full light s |
| Power Factor (Fraction)      | 0.9                  |
| Voltage (Nom)                | 120-277 V            |
| Temperature                  |                      |
| Ambient temperature range    | -4 °F to 113 °F      |
| T-Case Maximum (Nom)         | 122 °F               |
| Controls and Dimming         |                      |
| Dimmable                     | Yes                  |
| Mechanical and Housing       |                      |
| Product Length               | 1,200 mm             |
| Approval and Application     |                      |
| Energy Saving Product        | Yes                  |
| Suitable For Accent Lighting | No                   |

MasterClass LEDtube InstantFit T8

|                               |   |
|-------------------------------|---|
| Approval Marks                | UL certificate RoHS compliance DLC compliance |
| Energy Consumption kWh/1000 h | 18 kWh  |
| Product Data                  |   |
| Order product name            | 15T8/48-5000 IF 10/1 TAA                      |
| Full product name             | 15T8/48-5000 IF 10/1 TAA                      |
| Order code                    | 464271  |

|                                 |                |
|---------------------------------|----------------|
| Material Nr. (12NC)             | 929001158834   |
| Numerator - Quantity Per Pack   | 1              |
| EAN/UPC - Product/Case          | 046677464271   |
| Numerator - Packs per outer box | 10             |
| EAN/UPC - Case                  | 50046677464276 |

Dimensional drawing




| Product                  | D1          | D2         | A1           | A2          | A3          |
|--------------------------|-------------|------------|--------------|-------------|-------------|
| 15T8/48-5000 IF 10/1 TAA | 1-1/16 inch | 1-1/8 inch | 47-3/16 inch | 47-1/2 inch | 47-3/4 inch |


Photometric data



Spectral Power Distribution Colour - 15T8/48-5000 IF 10/1 TAA



Light Distribution Diagram - 15T8/48-5000 IF 10/1 TAA



General uniform lighting - 15T8/48-5000 IF 10/1 TAA

General uniform lighting - 15T8/48-5000 IF 10/1 TAA

## MasterClass LEDtube InstantFit T8

