



# Standard LED candles & lusters

## LEDBulb 4-40W E27 3000K 220-240V P45

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	4 W
Lighting Technology	LED	Lamp Current (Nom)	40 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	830 [CCT of 3000K]	Power Factor (Fraction)	0.5
Beam Angle (Nom)	150 degree(s)	Voltage (Nom)	220-240 V
Luminous Flux	350 lm	Temperature	
Color Designation	White (WH)	T-Case Maximum (Nom)	90 °C
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	95.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED candles & lusters

Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	LEDBulb 4-40W E27 3000K 220-240V P45
Full product name	LEDBulb 4-40W E27 3000K 220-240V P45
Full product code	871869653110500
Order code	929001160911


Material Nr. (12NC)	929001160911
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696531105
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696531112

Dimensional drawing




Product	D	C
LEDBulb 4-40W E27 3000K 220-240V P45	45 mm	87 mm


Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 3000K 220-240V P45



General uniform lighting - LEDBulb 4-40W E27 3000K 220-240V P45



Light Distribution Diagram - LEDBulb 4-40W E27 3000K 220-240V P45

## Standard LED candles & lusters

