



Standard LED candles & lusters

LEDBulb 4-40W E27 3000K 220V P45 3BC

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data

General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	4 W
Lighting Technology	LED	Lamp Current (Nom)	40 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	830 [CCT of 3000K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	150 degree(s)	Power Factor (Fraction)	0.5
Luminous Flux	350 lm	Voltage (Nom)	220-240 V
Color Designation	White (WH)	Temperature	
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	90 °C
Luminous Efficacy (rated) (Nom)	87.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted

Standard LED candles & lusters


Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDBulb 4-40W E27 3000K 220V P45 3BC
Full product name	LEDBulb 4-40W E27 3000K 220V P45 3BC
Full product code	871869678894300

Order code	929001160993
Material Nr. (12NC)	929001160993
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696788943
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696788950


Dimensional drawing

Product	D	C
LEDBulb 4-40W E27 3000K 220V P45 3BC	45 mm	87 mm


Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 3000K 220V P45 3BC



General uniform lighting - LEDBulb 4-40W E27 3000K 220V P45 3BC



Light Distribution Diagram - LEDBulb 4-40W E27 3000K 220V P45 3BC

Standard LED candles & lusters

