



# Standard LED candles & lusters

## LEDBulb 4-40W E27 6500K 220V P45 2BC

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	4 W
Lighting Technology	LED	Lamp Current (Nom)	40 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	865 [CCT of 6500K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	150 degree(s)	Power Factor (Fraction)	0.5
Luminous Flux	350 lm	Voltage (Nom)	220-240 V
Color Designation	Cool Daylight	Temperature	
Correlated Color Temperature (Nom)	6500 K	T-Case Maximum (Nom)	90 °C
Luminous Efficacy (rated) (Nom)	87.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted

Standard LED candles & lusters

Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDBulb 4-40W E27 6500K 220V P45 2BC
Full product name	LEDBulb 4-40W E27 6500K 220V P45 2BC
Full product code	871869678892900



Order code	929001161091
Material Nr. (12NC)	929001161091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696788929
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696788936

Dimensional drawing




Product	D	C
LEDBulb 4-40W E27 6500K 220V P45 2BC	45 mm	87 mm

Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 6500K 220V P45 2BC

General uniform lighting - LEDBulb 4-40W E27 6500K 220V P45 2BC



Light Distribution Diagram - LEDBulb 4-40W E27 6500K 220V P45 2BC

## Standard LED candles & lusters

