



Standard LED candles & lusters

LEDBulb 4-40W E27 6500K 220V P45 3BC

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	350 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	87.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

Standard LED candles & lusters

Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDBulb 4-40W E27 6500K 220V P45 3BC
Full product name	LEDBulb 4-40W E27 6500K 220V P45 3BC
Full product code	871869678896700


Order code	929001161093
Material Nr. (12NC)	929001161093
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696788967
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696788974

Dimensional drawing




Product	D	C
LEDBulb 4-40W E27 6500K 220V P45 3BC	45 mm	87 mm


Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 6500K 220V P45 3BC



General uniform lighting - LEDBulb 4-40W E27 6500K 220V P45 3BC



Light Distribution Diagram - LEDBulb 4-40W E27 6500K 220V P45 3BC

Standard LED candles & lusters

