



LEDLamps

LEDBulb 9.5-60W B22 3000K 230V A60 AU/PF

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information	
Cap-Base	B22 [B22]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	9.5-60W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	150 °
Luminous Flux (Nom)	806 lm
Luminous Flux (Rated) (Nom)	806 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color Consistency	<7
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	9.5 W
Lamp Current (Nom)	75 mA
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	10 kWh
Product Data	
Full product code	871869655949900
Order product name	LEDBulb 9.5-60W B22 3000K 230V A60 AU/PF
EAN/UPC - Product	8718696482124
Order code	929001163249
Numerator - Quantity Per Pack	1

LEDLamps

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001163249
Net Weight (Piece)	0.076 kg




Dimensional drawing



Basic Bulb A60 9W-60W 806lm 3000K B22 ND

Product	D	C
LEDBulb 9.5-60W B22 3000K 230V A60 AU/PF	60 mm	108 mm

Photometric data



A60 /830 FR

