



LEDLamps

LEDBulb 7-40W E27 6500K 230V A60 AU/PF

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


| General Information | |
|---------------------------------------|---------------------|
| Cap-Base | E27 [E27] |
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle | 50000X |
| Technical Type | 7-40W |
| Light Technical | |
| Color Code | 865 [CCT of 6500K] |
| Beam Angle (Nom) | 150 ° |
| Luminous Flux (Nom) | 600 lm |
| Luminous Flux (Rated) (Nom) | 600 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 6500 K |
| Luminous Efficacy (rated) (Nom) | 86 lm/W |
| Color Consistency | <7 |
| Color Rendering Index (Nom) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 7 W |
| Lamp Current (Nom) | 65 mA |
| Wattage Equivalent | 40 W |

| Starting Time (Nom) | 0.5 s |
|---------------------------------|--|
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.5 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 80 °C |
| Controls and Dimming | |
| Dimmable | No |
| Approval and Application | |
| Energy Efficiency Label (EEL) | A+ |
| Energy Saving Product | Yes |
| Suitable For Accent Lighting | No |
| Energy Consumption kWh/1000 h | 7 kWh |
| Product Data | |
| Full product code | 871869655957400 |
| Order product name | LEDBulb 7-40W E27 6500K 230V A60 AU/PF |
| EAN/UPC - Product | 8718696488348 |
| Order code | 929001163649 |
| Numerator - Quantity Per Pack | 1 |

LEDLamps

| | |
|---------------------------------|--------------|
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 929001163649 |
| Net Weight (Piece) | 0.076 kg |



Dimensional drawing




Basic Bulb A60 7W-48W 600lm 6500K E27 ND

| Product | D | C |
|--|-------|--------|
| LEDBulb 7-40W E27 6500K 230V A60 AU/PF | 60 mm | 110 mm |

Photometric data



LED Lamps, LEDBulb 7-40W A60 6500K 600lm



A60 /865 FR

