



LEDLamps

LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E27 [E27]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	50,000	Voltage (Nom)		220-240 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	T-Case Maximum (Nom)		70 °C
Light Technical		Controls and Dimming		
Color Code	865 [CCT of 6500K]	Dimmable		No
Beam Angle (Nom)	150 degree(s)	Mechanical and Housing		
Luminous Flux	1,055 lm	Bulb Finish		Frosted
Color Designation	Cool Daylight	Bulb Shape		A60 [A 60mm]
Correlated Color Temperature (Nom)	6500 K	Approval and Application		
Luminous Efficacy (rated) (Nom)	105.00 lm/W	Energy Saving Product		Yes
Color Consistency	<7	Suitable For Accent Lighting		No
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h		10 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data		
Operating and Electrical		Order product name		
Line Frequency	50 to 60 Hz	LEDBulb 10.5-75W E27 6500K 230V		
Input Frequency	50 to 60 Hz	A60AU/PF		
Power Consumption	10.5 W			
Lamp Current (Nom)	95 mA			

LEDLamps

Full product name	LEDBulb 10.5-75W E27 6500K 230V A60AU/PF
Full product code	871869648841600
Order code	929001163849
Material Nr. (12NC)	929001163849
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696488416
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696559628

Dimensional drawing



Product	D	C
LEDBulb 10.5-75W E27 6500K 230V A60AU/PF	60 mm	110 mm

Photometric data




General Uniform Lighting

General uniform lighting - LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

Light Distribution Diagram - LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

Spectral Power Distribution Colour - LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

Lifetime



Life Expectancy Diagram - LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

Lumen Maintenance Diagram - LEDBulb 10.5-75W E27 6500K 230V A60AU/PF

