



CorePro LEDspot MV

CorePro LEDspotMV 5-50W GU10 840 50D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data


General Information			
Cap-Base	GU10 [GU10]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	5 W
Switching Cycle	50,000	Lamp Current (Nom)	40 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	instant full light s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	No
Beam Angle (Nom)	50 degree(s)	Mechanical and Housing	
Luminous Flux	435 lm	Bulb Finish	White
Luminous Intensity (Nom)	400 cd	Bulb Shape	MR16 [2inch/50mm]
Color Designation	White (WH)	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Suitable For Accent Lighting	Yes
Luminous Efficacy (rated) (Nom)	80.00 lm/W	Energy Consumption kWh/1000 h	5 kWh
Color Consistency	<6	Product Data	
Color rendering index (CRI)	80	Order product name	CorePro LEDspotMV 5-50W GU10 840 50D
LLMF At End Of Nominal Lifetime (Nom)	70 %	Full product name	CorePro LEDspotMV 5-50W GU10 840 50D
Luminous Flux in 90° Cone (Rated)	400 lm		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

CorePro LEDspot MV

Full product code	871869649718000
Order code	929001172902
Material Nr. (12NC)	929001172902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696497180



Numerator - Packs per outer box	10
EAN/UPC - Case	8718696497197

Dimensional drawing



Product	D	C
CorePro LEDspotMV 5-50W GU10 840 50D	50 mm	55 mm

Photometric data



Light Distribution Diagram - CorePro LEDspotMV 5-50W GU10 840 50D

Spectral Power Distribution Colour - CorePro LEDspotMV 5-50W GU10 840 50D

